

# QC2600

## ZERO SPEED™ & UNDERWAY (P-SERIES) STABILIZER FIN

### DESCRIPTION:


A stabilizer fin is the device which develops the hydrodynamic forces needed to counter the roll motions of the vessel. The fin is installed on the stabilizer hull unit shaft, which serves as the axis about which the fin is deflected. Much like an airplane wing, as the fin is deflected, pressure differences result in a hydrodynamic force on the fin; this resultant force is used to counter-act the roll of the vessel during underway operations. During Zero Speed™ operations, the fin is quickly swung on demand to generate the needed counter-roll forces.

Designed based on extensive experience and model testing, the QC2600 P-series stabilizer fin is capable of significantly reducing vessel roll during both underway and Zero Speed™ operations.

### FEATURES:

- **SIMPLE INSTALLATION:** The fin is installed on the stabilizer hull unit shaft via a hydraulic coupling method. This attachment technique provides a durable and reliable connection, easily achieved with the use of supplied tools and instructions.
- **MINIMAL NOISE:** Quantum’s stabilizer fins are designed with innovative features such as minimal hull-to-fin clearances and trailing edge vortex generators. These elements help to reduce hydrodynamic noise and vibrations while underway.
- **ROBUST CONSTRUCTION:** The fins are fabricated of steel or stainless steel combined with strategic internal reinforcement. This interior bolstering enables the fin to withstand the cyclic loads encountered during operation.
- **MINIMAL MAINTENANCE:** The fin requires no maintenance during normal operation. The units are designed for maintenance intervals corresponding to vessel haul-outs every other year.

*Equipment is covered by Quantum’s 1 year comprehensive warranty.  
Service and technical support are available worldwide.*



<b>Typical Vessel Length*</b>	60-90m (197-295ft)
<b>Fin Size Range**</b>	7.0-9.0m <sup>2</sup> (75.3-96.8ft <sup>2</sup> )
<b>Typical Aspect Ratios</b>	0.36-0.40
<b>Typical Balance</b>	20-25%
<b>Dimensions</b>	See a Quantum Representative for Drawings

*\*Provided for reference only. Consult a Quantum representative for system sizing.*

*\*\* Size may be limited for higher speed vessels; see a Quantum representative for more information.*

*All information contained within this document remains the absolute property of the Quantum Group and is subject to change at any time. Any use of the information for other than the intended purpose is expressly forbidden. Consult a Quantum representative for more information.*

INNOVATION

